



RECYCLING INSTRUCTIONS

1

2

3

EU Code: 150110

EU Code: 160603

<p>LAPM 2</p>	<p>LAPG 1/4</p> <p>DIN 71412</p>	<p>LAPV 1/4</p>	<p>LAPV 1/8</p>	<p>LAPT 1000</p>	<p>LAPB D2 *</p>	<p>LAPB 5-16E1 *</p>	<p>LAPB 3x4E1 *</p>	<p>LAPB 3x7E1 *</p>	<p>LAPB 3x10E1 *</p>
----------------------	---	------------------------	------------------------	-------------------------	-------------------------	-----------------------------	----------------------------	----------------------------	-----------------------------

* Suitable for use with oil filled SYSTEM 24 units only

<p>LAPN 1/8</p>	<p>LAPN 1/4</p>	<p>LAPN 1/4UNF</p>	<p>LAPN 3/8</p>
<p>LAPN 1/2</p>	<p>LAPN 6</p>	<p>LAPN 8</p>	<p>LAPN 8x1</p>
<p>LAPN 10</p>	<p>LAPN 10x1</p>	<p>LAPN 12</p>	<p>LAPN 12x1.5</p>
<p>LAPF E1/4</p>	<p>LAPF M1/8</p>	<p>LAPF M1/4</p>	<p>LAPF M3/8</p>
<p>LAPP 4</p>	<p>LAPP 6</p>	<p>LAPC 50</p>	<p>LAPA 90</p>
<p>LAPE 35</p>	<p>LAPE 50</p>	<p>LAPA 45</p>	<p>LAPA 90</p>